

# **E0-1 Pump Packages**

#### **DESCRIPTION**

EO-1 is a versatile series of pumping units designed for use with virtually any type of intermittent lube system requiring oil flow up to 12 in³/min (200 cc/min). Each of these lube packages consists of a 115 or 230 volt AC, 50/60 Hz, single phase electric motor direct coupled to a gear pump and mounted on a steel or plastic reservoir. A wide range of reservoir sizes are available and all are equipped with a low level switch as standard. These pump assemblies are rated for service up to 580 psi (40 bar). See "Specifications" for additional details.

#### **FEATURES**

- Built in vent valve permits use with single line parallel systems.
- And adjustable internal relief protects pump from excessive pressures. Factory set at 580 psi (40 bar).
- Reservoir with removable covers, sized at 0.8, 1.6, 2.0 and 3.2 gallons (3, 6 and 12 liters).
- Reservoir has a visual level gauge, pressure gauge and filler/ strainer with screw on cap.
- Motor and low level switch meet EEC requirements (CE Mark compliance).



#### **OPERATION**

The motor/pump assembly on an EO-1 pump package runs whenever power is applied. On/off cycles are achieved by using an optional timer that has user selectable off and on times or control can be via the machine PLC where available and desired.

#### **APPLICATIONS**

The EO-1 is ideal for small to medium size series progressive of parallel systems requiring intermittent metered lubrication with an electrically driven pump. Combined with Trabon series progressive divider valves, LubriSystem Injectors, or Injecto-Flo Piston Distributors, the EO-1 can be operated on a timer, cycle switch, or pressure switch controlled cycle for precision lubrication.




Figure 1

SPECIFICATION	
Motor Voltage	115 ± 10% VAC, 50/60 Hz, 1ø 230 ± 10% VAC, 50/60 Hz, 1ø
Current Consumption	4.3A in-rush, 2.15A running @ 110 VAC, 1ø 1.9A in-rush, 0.9A running @ 220 VAC, 1ø
Motor Power	1/12 HP
Motor Speed	1680 RPM @ 60 Hz, 1ø 1340 RPM @ 50 Hz, 1ø
Pump Flow Rate	12 in <sup>3</sup> /min (200 cc/min), see chart below
Pressure	Relief valve protected 145-650 psi (10-45 bar) Factory set @ 580 psi (40 bar)
Oil Viscosity	ISO 50-1500 (SUS 250-5000)
Operation	Intermittent, 20% Duty Cycle @ max pressure (650 psi)

Low Level Switch	10 watt @ 110/220 VAC, 50/60 Hz, 1 pH Contacts (normal closed, held open)
Suction Strainer	100 mesh screen
Pressure Gauge	0-850 psi (0-60 bar)
Electrical Connections	Wire terminals in motor junction box, screw terminals in Low Level Switch connector
Reservoir Material	
Translucent Plastic	1 gallon polypropylene 2 gallon glass filled nylon 6-6
Metal	Painted steel with guarded glass level tube





Figure 2

Test oils = Mobile DTE Light - 158 SUS @  $100^{\circ}$ F (350 SUS @  $70^{\circ}$ F), Mobilgear 629 - 750 SUS @  $100^{\circ}$ F (2500 SUS @  $70^{\circ}$ F), Mobilgear 634 - 2337 SUS @  $100^{\circ}$ F (7500 SUS @  $70^{\circ}$ F)

#### **INSTALLATION DATA**

## **Mounting**

The entire lube package is installed with two 1/4" screws that pass through holes in the mounting flange at the top of the reservoir. Mounting dimensions are given in Figure 3 and Table 1.



**RELIEF VALVE AD-**JUSTMENT **FILL CAP** LOW LEVEL **SIDE** 6.89 (175)

**MOUNTING HOLE** CONFIGURATION

6.30 (160)

T<sub>O</sub>P

**6MM TUBE** 

(M12 X 1) DISCHARGE

**PORT** 

Figure 3.

Table 1

RESERVOIR SIZE	A DIM	B DIM	C DIM	D Dim	E DIM
.8 Gal. (3L) Plastic	12.76 (324)	7.25 (184)	5.31 (135)	7.28 (185)	9.06 (230)
1.6 Gal. (6L) Plastic	16.50 (419)	11.00 (279)	5.31 (135)	7.28 (185)	9.06 (230)
1.6 Gal. (6L) Metal	16.44 (4.18)	10.94 (278)	5.91 (150)	7.28 (185)	9.13 (232)
3.2 Gal. (12L) Metal	16.44 (418)	10.94 (278)	7.76 (197)	8.21 (209)	9.13 (232)

### **Electrical Hookup**

Figure 4 is a simplified schematic for the entire pumping unit. The electrical hookups are shown in Figures 5a, 5b and 5c. Wiring to the motor and switch should be with 16 AWG stranded wire and insulation rated for 115/230 VAC and 105°C.




Figure 4.






Figure 5b **MOTO TECHNICA 1 PH MOTORS** 





SCHEMATIC

ORDERING INFORMATION					
Description	Part No.	Old Part No.			
0.8 gallon (3 liter) Plastic Reservoir, 110V	562837	126-400-010			
0.8 gallon (3 liter) Plastic Reservoir, 220V	24B427	126-400-020			
1.6 gallon (6 liter) Plastic Reservoir, 110V	562839	126-400-030			
1.6 gallon (6 liter) Plastic Reservoir, 220V	562840	126-400-040			
1.6 gallon (6 liter) Metal Reservoir, 110V	562843	126-400-050			
1.6 gallon (6 liter) Metal Reservoir, 220V	_	126-400-060			
3.2 gallon (12 liter) Metal Reservoir, 110V	562844	126-400-070			
3.2 gallon (12 liter) Metal Reservoir, 220V	24B429	126-400-080			

NOTE: Motor voltages are 50/60 Hz and single phase.

SPARE PARTS ORDERING INFORMATION					
Description	Part No.	Old Part No.			
Adjustable Relief Valve	556015	126-410-007			
Gear Pump Only	556013	126-410-005			
Low Level Switch Assembly, 0.8 gallon	122117	126-410-013			
Low Level Switch Assembly, 1.6/3.2 gallon	556016	126-410-009			
Suction Strainer	556014	126-410-006			
Motor					
110 VAC	556011	126-410-000			
220 VAC	556012	126-410-001			
Pressure Gauge, 0-850 psi (0-60 bar)	_	126-410-011			
Adapter, M12 x 1(M) x 1/4 NPTF (FM)	_	435-702-471			

#### **MAINTENANCE INFORMATION**

Normally, the only maintenance required on EO-1 packages is filling the reservoir, and cleaning the suction strainer. Use only fresh, uncontaminated oil (ISO 18/14 cleanliness level) to fill the reservoir. Check the suction strainer annually, or more often if the pump is becoming noisy (cavitating) between cleaning. The suction strainer is accessed by removing the reservoir cover. It is also a good idea to periodically verify pump operation (lube delivery), the calibration of the timer settings and the actuation depth of the low level switch.

Graco endorses the SAE recommendation of ISO 18/14 (ISO 4406) oil cleanliness for most bearing applications. Some high speed bearings may require cleaner oil. Consult the bearing manufacturer for recommendation.

All written and visual data contained in this document are based on the latest product information available at the time of publication. Graco reserves the right to make changes at any time without notice.

## **Contact us today!**

To receive product information or talk with a Graco representative, call **800-533-9655** or visit us online at **www.graco.com**.

